





USB Connection

# Digital Microscope

**DIGITAL MICROSCOPE** (200x Model) 3R-MSUS B401・501 / (600x Model) 3R-MSUS B601


3R-MSUS B Series can show the images of what you see on PC through USB connection. There are LED lights on top to light up the object. Both still/movie could be measured with specific software.

Download the software and measure/adjust saved images




### Measurement

Set 2 points that you want to measure, and it will automatically output the result, even for degree of angle and acreage.



### Text

Insert the text of measurement data and remarks.



### Adjustment

Input actual range to automatically adjust measured value.

### ■ SPEC

OS	Windows10/8.1 Mac OS10	Light Sources	White LED×8
Camera	2M Pixel (401 / 601)	Magnification	Max : X=3.0mm, Y=2.2mm Range※1
	5M Pixel (501)		Max : X=2.3mm, Y=1.8mm Range※2
Sensor	1/3 CMOS Sensor (401 / 601)	Focus Adjustment	0 ~ 300mm (401 / 501)
	1/2.7 CMOS Sensor (501)		2 ~ 12mm (with Lens Cover) (601)
White balance / Exposure	Auto / Auto	Power	USB2.0 or above
Still pic size (bmp)	1600×1200、1280×960、640×480	Size	φ36x 103mm
	2592×1944 (501)、2048×1536 (501)	Cable Length	1.5m
Movie size (avi) (15fps)	1600×1200、1280×1024、640×480	Weight	100g
	2592×1944 (501)、2048×1536 (501)		

### ■ Accessories

- |                   |                   |
|-------------------|-------------------|
| <b>401 Model</b>  | <b>501 Model</b>  |
| Lens Cover 3types | Lens Cover 2types |
| • 60 / 200x       | • 60 / 200x       |
| • 100x            | • 100x            |
| • 80 / 150x       |                   |
| <b>601 Model</b>  | <b>All models</b> |
| Lens Cover 2types | • Stand           |
| • 500x            | • Holder          |
| • 600x            | • Simple Scale    |
|                   | • Installation CD |
|                   | • Instruction     |
|                   | • Warranty        |

※1 Require length of perpendicular of 36cm monitor to use 200x  
 ※2 Require length of perpendicular of 44cm monitor to use 200x  
 ※3 Require length of perpendicular of 36cm monitor to use 600x


**3R SYSTEMS CORP. JAPAN**

2F-2-8-30, Toko, Hakata, Fukuoka, Japan 812-0008

TEL: 092-260-3030 FAX: 092-441-4077

MAIL: info@3rrr-hd.jp 3rrr-btob.jp



Store